



S8VK-G24024

Book type power supply, Pro, 240 W, 24VDC, 10A, DIN rail mounting

Specifications

Type	Book type
Mounting method	DIN rail
Phase	Single
Power output	240 W
Efficiency	92 %
Output voltage	24 V
Rated output current	10 A
Power boost ratio	120 %
Temperature range	-40-70 °C
Terminal	Screw
Communication port(s)	None
Alarm function	-
Number of output branches	1
Rated supply voltage at AC 50 Hz	100-240 V
Allowable supply voltage AC	85-264 V
Allowable supply voltage DC	90-350 V
Product Width (unpacked)	60 mm
Product Height (unpacked)	125 mm
Product Depth (unpacked)	140 mm

S82Y-VK10F

Front-mounting bracket for S8VK (120, 240 and 480 W models)

Related products



Electronic Circuit Breaker

S8V-CP - Electronic Circuit Breaker



S8V-NF

Noise Filter S8V-NF

Downloads

CAD Library



Perfect Power Supply Solutions Brochure

EN PDF 807 KB



S8VK-G Switch Mode Power Supply Datasheet

EN PDF 9.76 MB



S8VK-S/S8FS-G Brochure

EN PDF 6.93 MB

