




ENGLISH

Datasheet

RS Pro 200cm Zinc Plated Steel Hydraulic Tubing, 1.5mm Wall Thickness, 370 bar, -40 to +120°C

RS Stock No: **432-5741**



Product Details

RS Pro hydraulic tubing of 200 cm, has steel construction with zinc plated finish for durability and corrosion resistance. The tube has 1.5 mm wall thickness, 370 bar maximum operating pressure and -40 to +120°C operating temperature. It is compatible with range of EO hydraulic tube fittings, for fluid applications.

Features and Benefits

- Steel construction
- Comes in zinc plated finish
- Operating temperature range of -40 to +120°C

**Specifications:**

Finish	Zinc Plated
Length	200 cm
Material	Steel
Maximum Operating Pressure	370 bar
Maximum Operating Temperature	+120°C
Minimum Operating Temperature	-40°C
Outside Diameter	15 mm
Wall Thickness	1.5 mm
Weight	0.641 kg/m
Special Feature	Seamless Tube
Tensile Strength	340 N/mm ²
Yield Point	235 N/mm ²