

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1552200133](#)
Status: **Active**
Overview: Flamar Standard and Custom Cables for Industrial Automation
Description: Flamar Control Cable, WSOR Jacket, Unshielded, 2 Circuits, 0.75mm² / 19 AWG, 6.00mm (.236") Diameter, 300.0m (984.25') Length, Black

Documents:

[Product Specification 1552200001-P1E \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

Agency Certification

UL E172949

General

Product Family Cable
Series [155220](#)
Comments 3 reels of 100.0m each
Crimp Quality Equipment Yes
Geographic Area Global
Overview [Flamar Standard and Custom Cables for Industrial Automation](#)
Product Name Flamar, Signal and Control
UPC 889056459273

Physical

Bending Radius - Minimum > 7.5xOD
Cable Length 300.0m
Circuits (Loaded) 2
Color - Cable Jacket Black
Insulation TPE
Material - Outer Jacket WSOR
Net Weight 0.047/kg
Outer Jacket Diameter 6.00mm
Packaging Type Reel
Temperature Range - Operating -25° to +80°C
Wire Size AWG 19
Wire Size mm² 0.75
Wire/Cable Type UL AWM 21215 / CSA

Electrical


Current - Maximum per Contact Contact Molex
Voltage - Maximum 600V

Material Info

Engineering Number B39-2-3X100M

Reference - Drawing Numbers

Product Specification 1552200001-P1E



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[155220](#) Series

Use With

DIN Valve Connectors [121201](#) , [121202](#)
, [121207](#) , [121208](#) , [121205](#) , [121211](#)

Micro-Change (M12) [120071](#)
Ultra-
Lock (M12) [120085](#)
GWconnect Heavy
Duty Connectors [93601](#)