


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES, UNLESS OTHERWISE SPECIFIED:

PANDUIT CT-1551 TOOL:

TOOL WEIGHT: 27.2 oz. [77] kg

Crimps most Panduit #22-#10 AWG insulated terminals & splices, and specific insulated disconnects.

Reduced crimp effort advantage for #12-#10 AWG terminations.

Provides UL Listed and CSA Certified terminations with applicable Panduit terminals.

DIMENSIONS SHOWN IN BRACKETS [] ARE METRIC, AND ARE FOR REFERENCE ONLY.

CRIMP POCKET AWG / mm ²	ENGLISH GO / NO GO GAGE MEMBERS		METRIC GO / NO GO GAGE MEMBERS	
	"G" Dia. (GO)	"NG" Dia. (NO GO)	"G" Dia. (GO)	"NG" Dia. (NO GO)
22-14/0,5-2,5	0.096"	0.106"	2,43 mm	2,69 mm
12-10/4,0-6,0	0.147"	0.155"	3,73 mm	3,93 mm

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	CT-1551 Contour Crimp™ Crimping Tool CUSTOMER DRAWING				
---	---	---	---	---	UPDATED THE LOGO ON THE TOOL FRAME, ADDED GO - NO GO CHART.	---	ITEM REVISION NAME: TP27603B01_01				MATERIAL: -----
01	2-10-17	BLR	BJPU	JADE	REMOVED PANDUIT LOGO AND MADE IN GERMANY FROM THE GRIPS;	4857/02	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.x) ± --- (.xxx) ± --- (.xx) ± --- ANGLES ± ---				
00	5-11-15	BLR	BJPU	ABJ	RELEASED	4857			DRAWING NUMBER: TP27603B01		
---	---	---	---	---	---	---	DRAWN BY: BLR	DATE: 5-11-15	CHK BJPU	SCALE NONE	SIZE SHT 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[CT-1551](#)