


Deep groove ball bearings, single row, seal on both sides



Principal dimensions			Basic load ratings		Fatigue load limit P_u	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	-
50	90	20	37,1	23,2	0,98	-	4800	0,46	6210-2RS1 *



Calculation factors

k_r 0,025

f_0 14