



Coding style table	
	Style A: For connectors 6 poles
	Style B: For connectors 10 and 14 poles
	Style C: For connectors from 16 to 64 poles



-Technical information available on a separate document ref: DS 09181100001
-Full range of P/N's and dimensions shown on page 2/2

	All Dimensions in mm Original Size DIN A3	Scale 2:1	Free size tol.		Ref.
	All rights reserved Department EC PD - FR	Created by DOUGE	Inspected by BAGDIKIAN	Standardisation HOFFMANN	Date 2014-05-16
HARTING Electronics GmbH D-32339 Espelkamp		Title SEK 18 male straight low profile			State Final Release
		Type TB	Number 09185XXX322		Doc-Key / ECM-Nr. 100565934/UGD/001/A 50000068837
				Rev. A	Page 1/2

		Performance Level			Dimensions		
		PL3	PL2	S4			
Nb of Contacts	Part Number	Part Number	Part Number	Insulator Color	A Max	B	E
06	0918 506 7322	0918 506 6322	0918 506 5322	Grey	15,4	12,78	2,54 x 2 = 5,08
10	0918 510 7322	0918 510 6322	0918 510 5322		20,5	17,86	2,54 x 4 = 10,16
14	0918 514 7322	0918 514 6322	0918 514 5322		25,6	22,94	2,54 x 6 = 15,24
16	0918 516 7322	0918 516 6322	0918 516 5322		28,1	25,48	2,54 x 7 = 17,78
20	0918 520 7322	0918 520 6322	0918 520 5322		33,2	30,56	2,54 x 9 = 22,86
26	0918 526 7322	0918 526 6322	0918 526 5322		40,8	38,18	2,54 x 12 = 30,48
30	0918 530 7322	0918 530 6322	0918 530 5322		45,9	43,26	2,54 x 14 = 35,56
34	0918 534 7322	0918 534 6322	0918 534 5322		51,0	48,34	2,54 x 16 = 40,64
40	0918 540 7322	0918 540 6322	0918 540 5322		58,6	55,96	2,54 x 19 = 48,26
50	0918 550 7322	0918 550 6322	0918 550 5322		71,5	68,66	2,54 x 24 = 60,96
60	0918 560 7322	0918 560 6322	0918 560 5322		84,2	81,36	2,54 x 29 = 73,66
64	0918 564 7322	0918 564 6322	0918 564 5322		89,3	86,44	2,54 x 31 = 78,74
06	0918 506 7322 001	0918 506 6322 001	0918 506 5322 001		Black	15,4	12,78
10	0918 510 7322 001	0918 510 6322 001	0918 510 5322 001	20,5		17,86	2,54 x 4 = 10,16
14	0918 514 7322 001	0918 514 6322 001	0918 514 5322 001	25,6		22,94	2,54 x 6 = 15,24
16	0918 516 7322 001	0918 516 6322 001	0918 516 5322 001	28,1		25,48	2,54 x 7 = 17,78
20	0918 520 7322 001	0918 520 6322 001	0918 520 5322 001	33,2		30,56	2,54 x 9 = 22,86
26	0918 526 7322 001	0918 526 6322 001	0918 526 5322 001	40,8		38,18	2,54 x 12 = 30,48
30	0918 530 7322 001	0918 530 6322 001	0918 530 5322 001	45,9		43,26	2,54 x 14 = 35,56
34	0918 534 7322 001	0918 534 6322 001	0918 534 5322 001	51,0		48,34	2,54 x 16 = 40,64
40	0918 540 7322 001	0918 540 6322 001	0918 540 5322 001	58,6		55,96	2,54 x 19 = 48,26
50	0918 550 7322 001	0918 550 6322 001	0918 550 5322 001	71,5		68,66	2,54 x 24 = 60,96
60	0918 560 7322 001	0918 560 6322 001	0918 560 5322 001	84,2		81,36	2,54 x 29 = 73,66
64	0918 564 7322 001	0918 564 6322 001	0918 564 5322 001	89,3		86,44	2,54 x 31 = 78,74

	All Dimensions in mm Original Size DIN A3	Scale 1:1	Free size tol.	Ref.
	All rights reserved Department EC PD - FR	Created by DOUGE	Inspected by BAGDIKIAN	Standardisation HOFFMANN
HARTING Electronics GmbH D-32339 Espelkamp		Title SEK 18 male straight low profile		Date 2014-05-16
		Type TB	Number 09185XXX322	State Final Release
			Doc-Key / ECM-Nr. 100565934/UGD/001/A 50000068837	Rev. A
			Page 2/2	