



E3FB-DP12 2M

Photoelectric sensor, M18 threaded barrel, metal, red LED, diffuse, 300 mm, PNP, Light-ON/Dark-ON, 2 m cable

Specifications

Shape	Cylindrical axial
Sensing method	Diffuse reflective
Sensing distance	300 mm
Setting method	Manual adjustment
Connection method	Cable
Cable length	2 m
Output type	PNP
Operation mode	Dark-ON, Light-ON
Response time	0.5 ms
Material housing	Brass, nickel plated
Thread size	M18
Product Length (unpacked)	44 mm
Type of light	Polarity free red light
Power supply voltage	10-30 V
Degree of protection (IP)	IP67/IP69K

Accessories



E39-L183

M18 L-type mounting bracket, stainless steel (SUS304)

CAD Library



E3FA Brochure

EN PDF 5.67 MB



E3FA/E3RA/E3FB/E3RB Photoelectric Sensors Datasheet

EN PDF 6.64 MB