



Tactical Light 700

The Energizer® TAC 700 delivers high performance in a durable, dependable, and compact body. The rear push button, strobe mode, and durable aircraft grade aluminum were designed to work on various situations. In addition, the light output and 4 different modes (High, Medium, Low, Emergency Strobe), make it perfect for any outdoors and indoors usage, including work and DIY projects. Stay prepared in emergency situations with this light's strike bezel head. Its removable clip works in both orientations which provides the versatility to clip and use the way works best for you.

Specifications

	high	medium	low
Lumeny (jasność)	700 Lumens	100 Lumens	20 Lumens
Czas działania	2 Hours	15 Hours	35 Hours
Zasięg	100	NA	NA
Odporność na warunki atmosferyczne (wodoszczelno)	IPX4		
odporność na uderzenia	1 M		

Features

- Durable Aircraft Grade
- Aluminum Rear push button to easily change modes while holding the light.
- Compact size and lightweight
- Removable Clip that works in both orientations
- Strike Bezel Head
- Light modes : high , medium , low

Logistics

SAP	E301528100
MODEL NUMBER	PMHT2L
EAN	7638900426472
CU/SU	4
CU DIMENSIONS (cm) (H,W,D)	24 x 10.8 x 5.2
SU DIMENSIONS (cm) (H,W,D)	25 x 12 x 23
WEIGHT (g) CU	176 g
SU DETAILS	tray
BATTERIES	2CR123

Palletisation

	Battery	CU	SU	DU	XU	Pallet Layer	Pallet	↙ cm	↘ cm	↙ cm	Gross kg	Net kg
Battery												
CU	2							5.2	10.8	24	176	176
SU	8	4						12	23	25	0.86	704
DU	0		0									0
XU	0		0	0								0
Pallet Layer	240	120	30	0	0			80	120	25	25.8	21120
Without wood pallet	720	360	90	0	0	3		80	120	75	77.4	63360
With wood pallet	720	360	90	90	0	3		80	120	264	99.4	63360