

Кнопка тактовая WSTP7750-250AR



Detail Specification

Series NO. WSTP77HS
H=5.0,7.0,9.9mm...

1. Rating: 50mA 12VDC
2. Contact Resistance : 50mΩ max(initial)
3. Insulation Resistance: 100MΩ(minDC 250V)
4. Dielectric Strength : AC250V(50/60Hz for 1minute)
5. Electrically Life: 50,000cycles
6. Environment temperature: -25°c-70°c
7. Operating Force: 180/250(±20gf)
8. IP protection level: IP67

