

<b>CUSTOMER DATA SHEET</b>	Status: <b>Approved</b>
CDS No: 25673, 25679, 25685, 25688, 25692, 25694	Date: <b>14/01/11</b>
Product <b>JACKSON* Safety Nemesis V30 Eye Protection</b>	Replaces: <b>New</b>



PRODUCT (All Variants)	
Regulatory Compliance	EN 166:2001
Authorised Body	INSPEC 0194
Optical Class	Class 1 (Continuous Use)
Mechanical Strength	Class F (Low Energy 45m/s)
Extremes of Temperature	T (-5 deg C to + 55 deg C)
Weight	27 (g)

Ocular/Lens Type, Scale Filter Numbers (Filter Type)	
Amber	2-1.2 (UV Filter colour recognition may be affected)
Clear Anti-Fog	2-1.2 (UV Filter colour recognition may be affected)
Indoor/Outdoors	5-1.7(Sunglare filter without infra-red specification)
Smoke Mirror	5-3,1 (Sunglare filter without infra-red specification)
IRUV 3.0	3 (Welding)
IRUV 5.0	5 (Welding)

Ocular/Lens Markings and Frame Marking		
Lens Variant	Lens	Frame
Amber (25673)	CE, 2-1.2,KC,1,FT	CE, KC, EN166 FT
Clear Anti-Fog (25679)	CE, 2-1.2,KC,1,FT	CE, KC, EN166 FT
Indoor/Outdoors (25685)	CE, 5-1.7,KC,1,FT	CE, KC, EN166 FT
Smoke Mirror (25688)	CE, 5-3.1,KC,1,FT	CE, KC, EN166 FT
IRUV 3.0 (25692)	CE, 3,KC,1,FT	CE, KC, EN166 FT
IRUV 5.0 (25694)	CE, 5,KC,1,FT	CE, KC, EN166 FT

PACKAGING	
Unit of sale: Corrugated box	1 pair of glasses/poly bag 12 polybags per sales unit and 12 sales units per transit outer (144 pairs of glasses)
Sales Unit Size 16.5 x 10.6 x 29.8 cm	Net (gross) Weight/Box 0.324 Kg (0.522 Kg)

ADDITIONAL INFORMATION
Please refer to the information included in the product insert. Data generated from samples taken to be typical of standard product. The data is given for information only. Additional information can be supplied on request.

CONFIDENTIALITY STATEMENT
These specifications and the confidential information contained herein are the property of Kimberly-Clark. Copies of this material are the property of Kimberly-Clark and should be made only if necessary. Copies and original are considered trade secrets.