

Specification Sheet

Part Number: 113-00060



Reinforcement ribs between the screw mount and cable tie head provide additional strength for added bundle stability and security. Simple one piece design for quick and easy installation.

Secures with a screw or bolt.

1-Pc Cable Tie/Screw Mount, 8.5" Long, .2" Hole, 1.8" Max Bundle Dia, 50lb, PA66HS, Black, 100/pkg

Article Number 113-00060

Type T50MRX

Color Black (BK)

Quantity Per bag

Product Description Screw Mount Cable Ties attach to existing holes using a screw or bolt to provide a fastening point to secure and route wire and cable bundles. Reinforced ribs between the screw mount and cable tie head provide additional strength for added bundle stability and security.

Short Description 1-Pc Cable Tie/Screw Mount, 8.5" Long, .2" Hole, 1.8" Max Bundle Dia, 50lb, PA66HS, Black, 100/pkg

Global Part Name T50MRX-PA66HS-BK

Minimum Tensile Strength (Imperial) 50.0

Minimum Tensile Strength (Metric) 225.0

Length L (Imperial) 8.0

Length L (Metric) 203.2

Fixation Method Fixing hole

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.2

Width W (Metric) 4.7

Bundle Diameter Min (Imperial) 0.06

Bundle Diameter Min (Metric) 1.5

Bundle Diameter Max (Imperial) 1.77

Bundle Diameter Max (Metric) 45.0

Height H (Imperial)	.24
Height H (Metric)	6.0
Mounting Hole Diameter D (Imperial)	0.2
Mounting Hole Diameter D (Metric)	5.2 mm
Mounting Hole Diameter D Max (Metric)	5.2

Material Polyamide 6.6 heat stabilized (PA66HS)

Material Shortcut PA66HS

Flammability UL 94 V-2

Operating Temperature -40°F to +257°F (-40°C to +125°C)

ROHS Compliant Yes

UL Recognized (US) Yes

UL Listed (US and Canada) Yes

UL Recognized (US and Canada) Yes

UL Listed (US) Yes

Package Quantity (Imperial) 100

Package Quantity (Metric) 100

Customs Number 3926909988