

Specification Sheet

Part Number: RT40R9C2



Special design with extended pawl offers a release feature for quick and easy access to wire bundles.

Head design provides high tensile strength with very low insertion force even after repeated use.

Releasable Cable Tie, Release Tab, 8.5" Long, 40 lb Tensile Strength, PA66, Natural, 100/pkg

Article Number 115-06219

Type RT40R

Color Natural (NA)

Quantity Per bag

Product Description HellermannTyton releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes are necessary. The head design guarantees high tensile strength even after repeated use, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description Releasable Cable Tie, Release Tab, 8.5" Long, 40 lb Tensile Strength, PA66, Natural, 100/pkg

Global Part Name RT40R-PA66-NA

Minimum Tensile Strength (Imperial) 40.0

Minimum Tensile Strength (Metric) 180.0

Length L (Imperial) 8.5

Length L (Metric) 215.9

Identification Plate Position none

Releasable Closure Yes

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.16

Width W (Metric) 4.0

Bundle Diameter Min (Imperial) 0.06

Bundle Diameter Min (Metric) 1.5

Bundle Diameter Max (Imperial) 2.0

Bundle Diameter Max (Metric) 51.0

Thickness T (Imperial) 0.05

| | |
|--------------------------------------|----------------------------------|
| Thickness T (Metric) | 1.2 |
| Material | Polyamide 6.6 (PA66) |
| Material Shortcut | PA66 |
| Flammability | UL 94 V-2 |
| Operating Temperature | -40°F to +185°F (-40°C to +85°C) |
| Reach Compliant (Article 33) | Yes |
| ROHS Compliant | Yes |
| Certification/Specification | UL-ZODZ2.E64139 |
| UL Recognized (US) | Yes |
| UL Recognized (US and Canada) | Yes |
| Package Quantity (Imperial) | 100 |
| Package Quantity (Metric) | 100 |
| Customs Number | 3926909988 |

