


Specification Sheet

Part Number: 132-00009



Unique two piece tie allows parallel entry and exit through the head for easy assembly.

High impact, heat stabilized material gives strength needed for trucking and heavy equipment applications.

Button Head Cable Tie with Retainers and Pilot Bushings, 15.0" Long, PA66HIRHSUV, Black, 50/pkg

Article Number 132-00009

Type BT130LDP

Color Black (BK)

Quantity Per bag

Product Description The button head tie is a two piece tie providing for parallel entry and exit through the head. The strap contains serrations on both sides, and has two opposed pawls recessed within a domed head. This design allows the strap to be directed clockwise or counter-clockwise prior to insertion into the head, enabling bi-directional looping.

Short Description Button Head Cable Tie with Retainers and Pilot Bushings, 15.0" Long, PA66HIRHSUV, Black, 50/pkg

Global Part Name BT130LDP-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial) 130.0

Minimum Tensile Strength (Metric) 578.0

Length L (Imperial) 15.0

Length L (Metric) 381.5

Fixation Method Connector Clip

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Outside Serrated

Width W (Imperial) 0.3

Width W (Metric) 7.6

Bundle Diameter Min (Imperial) 0.25

Bundle Diameter Min (Metric) 6.4

Bundle Diameter Max (Imperial) 4.33

Bundle Diameter Max (Metric) 110.0

Mounting Hole Diameter D (Metric)	25.4 mm
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Material Head	Polyamide 6.6 heat stabilized (PA66HS)
Flammability	UL 94 HB
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3926909988