

Specification Sheet

Part Number: T150LL0X2

Engineered and manufactured for maximum performance and quality. Made from 100% high-quality plastic to ensure efficient recycling.

Inside serration for a strong grip onto bundles.

Easy application either manually or with a tensioning tool.

Bent tail allows for simpler insertion.



Heavy Duty Cable Tie, 36" Long, UL Rated, 175lb Tensile Strength, PA66, Black, 25/pkg

Article Number 111-15700

Type T150LL

Color Black (BK)

Quantity Per bag

Product Description HellermannTyton heavy duty cable ties offer a higher tensile strength for heavy load applications. The head design guarantees high tensile strength, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description Heavy Duty Cable Tie, 36" Long, UL Rated, 175lb Tensile Strength, PA66, Black, 25/pkg

| | |
|--|-----------------|
| Global Part Name | T150LL-PA66-BK |
| Minimum Tensile Strength (Imperial) | 175.0 |
| Minimum Tensile Strength (Metric) | 780.0 |
| Length L (Imperial) | 36.0 |
| Length L (Metric) | 925.0 |
| Identification Plate Position | none |
| Releasable Closure | No |
| Tie Closure | plastic pawl |
| Variant | Inside Serrated |
| Width W (Imperial) | 0.35 |
| Width W (Metric) | 8.9 |
| Bundle Diameter Min (Imperial) | 0.31 |
| Bundle Diameter Min (Metric) | 8.0 |
| Bundle Diameter Max (Imperial) | 10.8 |
| Bundle Diameter Max (Metric) | 274.3 |

| | |
|--------------------------------------|----------------------------------|
| Material | Polyamide 6.6 (PA66) |
| Material Shortcut | PA66 |
| Flammability | UL 94 V-2 |
| Halogen Free | Yes |
| Operating Temperature | -40°F to +185°F (-40°C to +85°C) |
| ROHS Compliant | Yes |
| Certification/Specification | UL-ZODZ2.E64139 |
| UL Recognized (US) | Yes |
| UL Listed (US and Canada) | Yes |
| UL Recognized (US and Canada) | Yes |
| UL Listed (US) | Yes |
| Package Quantity (Imperial) | 25 |
| Package Quantity (Metric) | 25 |
| Customs Number | 3926909988 |

