


Specification Sheet

Part Number: T50IDH0UVC2



The tie contains a dual locking design to secure two bundles at once. Head design can also provide spacing between parallel bundles.

Bent tail allows for quick insertion into head.

Double-Head Cable Tie, 12" Long, 50lb Tensile Strength, PA66UV, Black, 100/pkg

Article Number 117-05360

Type T50IDH

Color Black (BK)

Quantity Per bag

Product Description The double head cable tie was designed with a dual locking head that creates two loops to secure two bundles simultaneously. The head also provides separation between bundles or bundles running parallel to each other. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description Double-Head Cable Tie, 12" Long, 50lb Tensile Strength, PA66UV, Black, 100/pkg

Global Part Name T50IDH-PA66UV-BK

Minimum Tensile Strength (Imperial) 50.0

Minimum Tensile Strength (Metric) 225.0

Length L (Imperial) 12.0

Length L (Metric) 305.0

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.19

Width W (Metric) 4.7

Bundle Diameter Min (Imperial) 0.06

Bundle Diameter Min (Metric) 1.6

Bundle Diameter Max (Imperial) 3.0

Bundle Diameter Max (Metric) 76.2

Bundle Diameter 1st Loop Max (Imperial) 3.0

Bundle Diameter 1st Loop Max (Metric) 76.2

Bundle Diameter 2nd Loop Max (Imperial) 1.5

Bundle Diameter 2nd Loop Max (Metric) 38.1

Thickness T (Imperial) 0.055

Thickness T (Metric) 1.4

Material Polyamide 6.6 UV-resistant (PA66UV)

Material Shortcut PA66UV

Flammability UL 94 V-2

Halogen Free Yes

Operating Temperature -40°F to +185°F (-40°C to +85°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Certification/Specification UL | ANSI/UL 746B UL | ANSI/UL 1565 UL | ANSI/UL 62275

UL Recognized (US) Yes

UL Recognized (US and Canada) Yes

Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988