

Specification Sheet

Part Number: 157-00106



Head allows for a 0.2" lateral adjustment on stud during installation. Quick and easy installation ideal for manufacturing environment.

1-Pc Cable Tie/Oval Stud Mount, 6.6" Long, 50lb Tensile, Without Thumb Bar, PA66HS, Black, 3000/pkg

Article Number	157-00106
Type	T50SOSSB5-High-E-O-US
Color	Black (BK)
Quantity Per	bag
Product Description	Oval Shaped Stud Mount's special design allows for a 0.2" (5.5 mm) lateral adjustment, allowing for any misalignment of the stud or incorrect position of the tie on the cables. The mount allows it to be installed onto a weld stud without the use of any tools.
Short Description	1-Pc Cable Tie/Oval Stud Mount, 6.6" Long, 50lb Tensile, Without Thumb Bar, PA66HS, Black, 3000/pkg
Global Part Name	T50SOSSB5-High-E-O-US-PA66HS-BK

Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	225.0
Length L (Imperial)	6.6
Length L (Metric)	167.0
Fixation Method	Weld Stud Fixing
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Width W (Imperial)	0.2
Width W (Metric)	5.0
Bundle Diameter Min (Imperial)	0.04
Bundle Diameter Min (Metric)	1.0
Bundle Diameter Max (Imperial)	1.38
Bundle Diameter Max (Metric)	35.0
Stud Diameter (Metric)	5.0 mm
Stud Diameter (Imperial)	0.20

Material Polyamide 6.6 heat stabilized (PA66HS)

Material Shortcut PA66HS

Flammability UL 94 V-2

Operating Temperature -40°F to +257°F (-40°C to +125°C)

ROHS Compliant Yes

Package Quantity (Imperial) 3000

Package Quantity (Metric) 3000

Customs Number 3926909988