

	Netac	Netac	Netac	Netac
	68 æ	32 GB	64 GB ≈	128 GB 221
OGB	CLASS	CLASS	CLASS	CLASS

Capacity	Performance		
8GB	C10 Up to 20MB/s read**		
16GB~128GB	C10, U1 Up to 80MB/s read **		

Netac P600 SDHC/SDXC Memory Card

Netac P600 SDHC and SDXC memory cards offer enough storage space for tablets, action cameras, drones, and more devices, is a great choice for capturing and storing your favorite pictures and videos. P600 cards also with waterproof, shockproof, and temperature features and a five-year limited warranty.





Advanced speeds performance

Class 10, U1 performance with reading speeds up to 80MB/s.

Multi-device compatibility

Support different devices such as PCs, laptops, cameras, drones, Nintendo Switch, GoPro, etc.





Shockproof



IPX7 Waterproof

Highlights

· High compatibility across multiple devices

X-ray-proof

- Connector: UHS-I (SDR104)
- Read speeds up to 80MB/s*
- Large capacity options up to 128GB
- · Compatible with game consoles
- Support full HD video recording
- Offer 4 trustworthy protections
- Salt Spray Grade: GB/T 2423.17
- Anti-static Grade: GB/T 17626.2
- Drop Test: GB/T 2423.8

Product Specification

Capacity	8GB/16GB/32GB/64GB/128GB		
Form Factor	SDHC™/SDXC™		
Standard	SD 3.01		
R/W Performance	8GB up to 20MB/s read* 16GB-128GB up to 80MB/s read*		
Speed Class	Class 10 / U1		
Dimension	32mm*24mm*2.1mm		
Operating Temperature	0°C ~ 70°C		
Storage Temperature	-25°C ~ 85°C		
Warranty	5-year Limited		
Part Numbers	NT02P600STN-008G-N/R NT02P600STN-016G-N/R NT02P600STN-032G-N/R NT02P600STN-064G-N/R NT02P600STN-128G-N/R		