

Capacity	Performance
16GB~32GB	C10, U1, A1 Up to 90MB/s read**
64GB~512GB	C10, V30, A1 Up to 90MB/s read**

Netac P500 Extreme Pro MicroSD Flash Memory Card

The Netac P500 Extreme Pro microSD is a highly durable memory card. The cards come with Class 10 speed and capacities up to 512GB to meet the high-definition HD video recording and photo capturing, perfect choice for photographers, videographers, filmmaker and more. It also can smoothly work in extreme environments, so no worries about how harsh environments will be.

Fast transfer performance

Powerful Class 10 speeds with reading speeds up to 90MB/s, easily download and transfer.

High-speed shooting

It supports 4KUHD and full HD videos capturing.

Highest grade durability

Netac P500 Extreme Pro card is with temperature- proof, waterproof, shock-proof, and x-ray-proof features.









Highlights

- Type: SDXC/SDHC, Class 10, U1, V30
- Transfer speeds of up to 90MB/s*
- Max 512GB storage
- A1 apps speed performance
- · Capture 4K Ultra HD and full HD video
- · Water, heat, shock, and x-ray proof
- Fully compatible with smartphones, tablets, cameras, GoPro, action cameras, laptops, desktop computers, DSLRs, drones, Nintendo Switch and more devices

Netac	Netac 128
128 128	

Product Specification	
Capacity	16GB/32GB/64GB 128GB/256GB/512GB
Form Factor	microSDHC™/microSDXC™
Standard	SD 3.01
R/W Performance	Up to 90MB/s read**
Speed Class	Class 10 , U1 , V30
Dimension	15mm*11mm*1.0mm
Operating Temperature	0°C ~ 70°C
Storage Temperature	-25°C ~ 85°C
Warranty	5-year Limited
Part Numbers	NT02P500PRO-016G-N/S/R NT02P500PRO-032G-N/S/R NT02P500PRO-064G-N/S/R NT02P500PRO-128G-N/S/R NT02P500PRO-256G-N/S/R NT02P500PRO-512G-N/S/R