



Electric Data		
Characteristic Impedance	50ohm, 75ohm	
Frequency Range	0-4GHz	
Working Voltage	500 VRMS(max at sea level)	
Dielectric Withstanding Voltage	1500 VRMS(min at sea level)	
VSWR	≤1.30	
Contact Resistance	Inner: 1.5 milliohms(max) Outer: 1 milliohms(max)	
Insulation Resistance	5000 megohms(min)	
Mechanical Data		
Durability Mating	500 Cycles min.	
Material Data		
Connector Parts	Materials	Plating Finish
Body	Brass	Nickel
Male Pin	Brass	Gold
Insulators	PTFE	N/A
Environmental Data		
Temperature Range	-65~+165°C	