


## Specification Sheet

Part Number: MB310C2



Compact size fits most mounting applications.

Simple to install with a screw or rivet.

Single hole attachment with two-way entry for cable tie.

Screw Mount Cable Tie Base, .75" x .75", .14" Max Tie Width, .12" Hole Dia, PA66, White, 100/pkg

**Article Number** 151-28302

**Type** MB3

**Color** White (WH)

**Quantity Per** bag

**Product Description** These cable tie mounts are compact in size. They are designed for simple yet robust installation. They pair with a cable tie for mounting applications including telecom equipment, switchgear and control cabinets.

**Short Description** Screw Mount Cable Tie Base, .75" x .75", .14" Max Tie Width, .12" Hole Dia, PA66, White, 100/pkg

**Global Part Name** MB3-PA66-WH

<b>Length L (Imperial)</b>	0.75
<b>Length L (Metric)</b>	19.0
<b>Fixation Method</b>	Screw Mounting and Rivet
<b>Width W (Imperial)</b>	0.75
<b>Width W (Metric)</b>	19.0
<b>Cable Ties</b>	T18 - T30
<b>Height H (Imperial)</b>	.15
<b>Height H (Metric)</b>	3.80
<b>Cable Tie Width Max (Imperial)</b>	0.14
<b>Cable Tie Width Max (Metric)</b>	3.6
<b>Mounting Hole Diameter D (Imperial)</b>	0.12
<b>Mounting Hole Diameter D (Metric)</b>	3.0 mm
<b>Mounting Hole Diameter D Max (Metric)</b>	3.0
<b>Mounting Hole Centers (Imperial)</b>	0.52

<b>Material</b>	Polyamide 6.6 (PA66)
<b>Material Shortcut</b>	PA66
<b>Flammability</b>	UL 94 V-2
<b>Operating Temperature</b>	-40°F to +185°F (-40°C to +85°C)
<b>ROHS Compliant</b>	Yes
<b>Certification/Specification</b>	UL
<b>UL Recognized (US)</b>	Yes
<b>UL Recognized (US and Canada)</b>	Yes
<b>Package Quantity (Imperial)</b>	100
<b>Package Quantity (Metric)</b>	100
<b>Customs Number</b>	3926909988