

Specification Sheet

Part Number: CTM410C2



KR/CTM series are designed to provide stability to wire bundles. These mounts can accommodate miniature, intermediate, or standard cross-section cable ties.

Each mount is secured with a single screw.

| | |
|----------------------------|---|
| Article Number | 151-30703 |
| Type | CTM4 |
| Color | White (WH) |
| Quantity Per | bag |
| Product Description | Designed specifically for holding heavier cable bundles these mounting bases can be used in many industries from agriculture to truck manufacture. They offer a very secure fixing and can be used with a wide variety of heavy duty cable ties up to 8.3 mm width. |
| Short Description | Cable Tie Anchor Mount, .86" x .62", .25" Hole Dia, .31" Max Tie Width, PA66, White, 100/pkg |
| Global Part Name | CTM4-PA66-WH |

| | |
|--|--------------------------|
| Length L (Imperial) | 0.86 |
| Length L (Metric) | 21.8 |
| Fixation Method | Screw Mounting and Rivet |
| Width W (Imperial) | 0.62 |
| Width W (Metric) | 15.8 |
| Cable Ties | T18 - T120 |
| Height H (Imperial) | .37 |
| Height H (Metric) | 9.40 |
| Cable Tie Width Max (Imperial) | 0.31 |
| Cable Tie Width Max (Metric) | 7.9 |
| Mounting Hole Diameter D (Imperial) | 0.25 |
| Mounting Hole Diameter D (Metric) | 6.4 mm |
| Mounting Hole Diameter D Max (Metric) | 6.4 |
| Material | Polyamide 6.6 (PA66) |

| | |
|--------------------------------------|--|
| Material Shortcut | PA66 |
| Flammability | UL 94 V-2 |
| Operating Temperature | -40°F to +185°F (-40°C to +85°C) |
| Reach Compliant (Article 33) | Yes |
| ROHS Compliant | Yes |
| Certification/Specification | UL ANSI/UL 746B UL ANSI/UL 1565 UL ANSI/UL 62275 |
| UL Recognized (US) | Yes |
| UL Recognized (US and Canada) | Yes |
| Package Quantity (Imperial) | 100 |
| Package Quantity (Metric) | 100 |
| Customs Number | 3926909988 |