

[Power Cords](#)

Pwr Cord, 10A, 230V, C14 to UK rec



APC Power Cords , Input: 230V , Input Connections: IEC-320 C14 , Cord Length: 2 feet (0.61 meters) , Output Connections: BS 1363

Standard Lead Time : Usually in Stock

AP9881

[✉ Email Technical Specifications](#)

[🖨 Printer Friendly](#)

Technical Specifications

Product Overview

Documentation

Options

Compare Models

Output

Maximum Total Current Draw per Phase 10A

Output Connections (1) BS 1363

Input

Nominal Input Voltage 230V

Input Connections IEC-320 C14

Cord Length 0.61 meters

Number of Power Cords 1

Maximum Line Current per phase 10A

Physical

Net Weight 0.36 KG

Shipping Weight 0.45 KG

Shipping Height 305.00 mm

Shipping Width 102.00 mm

Shipping Depth 102.00 mm

Color Black