

Search within category

GO

BUY NOW

DESIGN / INSTALL



FSD77-8-K

Insulated ferrules, single wire red DIN end sleeve on mini-reel, 18 AWG (1.0mm²), 0.31" (8.0mm) pin length.

Specs

Tools

Documents

★ Add to Favorites

🛒 Add to BOM

Std. Pkg. Qty.	1000
Product Type	Ferrules on Reel
Pin Length In. (mm)	0.31 (8)
Style	Single Wire
Wire Range In. (mm ²)	18 AWG (1)
Barrel Type	Seamless
Base Material	Copper
Insulation	Polypropylene
Length (In.)	0.57
Length (mm)	14.5
Panduit Color Code	Red
Plating Type	Tinned
Part Number Series	FSD
Length In (mm)	0.57 (14.5)
Max. Insulation Diameter In. (mm)	0.12 (3)
Wire Strip Length In. (mm)	13/32" (.4062) - (10mm)
Flammability Rating	HB
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)
Tool	CP-881, CA10, Uni-A-FA (SCA-712022002)
CSA Certified	C22.2 No. 291-14
Standards	DIN 46228 Part 1, UL 486F Listed, UL 508A Certified
Packaging Type	Mini Reel
Pieces Per Reel	1000
CE Compliant	No
Inside Diameter (In.)	0.06
Inside Diameter (mm)	1.5
Outside Diameter (In.)	0.07
Outside Diameter (mm)	1.8
Part Features	<ul style="list-style-type: none"> • Polypropylene insulation housing available in DIN standard colors in reels to 3000 or 5000 • Designed specifically for use with the Ferrule Applicator (CA10) for high volume applications • Continuously molded design provides consistent placement of ferrules in applicator to ensure fast, reliable terminations
Wire Range	18 AWG
RoHS Compliancy Status	Compliant
Min. Order Qty.	1,000.0000