


DESCRIPTION: POWER / SIGNAL - SOLDER CUP - FEMALE - MACHINED



SPECIFICATIONS:

ELECTRICAL: INSULATOR RESISTANCE: 5 GOhms MIN. DIELECTRIC WITHSTANDING: 1000 VAC FOR 1 MIN **OPERATING TEMPERATURE:** -55°C TO +125°C POWER CONTACT RESISTANCE: 2.0 mOhms MAX. 10 mOhms MAX. SIGNAL CONTACT RESISTANCE: POWER CONTACT AMPERAGE: SEE P/N KEY SIGNAL CONTACT AMPERAGE: 5 AMPS MECHANICAL: 4.5 Kg MAX. CONTACT INSERTION FORCE: 0.3 Kg MIN. CONTACT SEPARATION FORCE: MATERIALS: CONTACTS: COPPER ALLOY, GOLD FLASH INSULATOR: PBT UL94V-0 RATED 230°C PROCESS TEMP. SHELL: NICKEL PLATED STEEL SEAL: F04 FLEXIBLE ADHESIVE





(SEE PAGE 2 FOR SEALING DETAILS)



