

Screw plug


10xx M/G

Screw plug	Brass CuZn39Pb3, nickel-plated
O-ring	Nitrile rubber NBR
Connecting thread	Pg as per DIN 40430




Properties

Temperature range	-40 °C +100 °C
Protection grade	IP66 / IP68 - 5 bar
	<ul style="list-style-type: none">for secure sealing of unused threaded or clearance hole



Features

round

A	L	Da	H	 VPE	Part No.
Pg 7	4,5	16	7	100	1007 M/G
Pg 9	4,5	19	8	100	1009 M/G
Pg 11	4,5	22	8	100	1011 M/G
Pg 13,5	6	24	10	100	1013 M/G
Pg 16	6	26	10	100	1016 M/G
Pg 21	6,5	32	10	100	1021 M/G
Pg 29	8	39	12	50	1029 M/G
Pg 36	9	50	15	25	1036 M/G
Pg 42	10	57	16	25	1042 M/G
Pg 48	10	64	16	10	1048 M/G