

DisplayPort Cable with Latches, 4K @ 30 Hz, (M/M) 20 ft. (6.09 m)

MODEL NUMBER: P580-020



Highlights

- Digital Video and Audio in one cable
- Supports Ultra High Definition (UHD) 4K x 2K video resolutions up to 3840 x 2160 @ 30Hz, including 1080p
- Small footprint compared to VGA or DVI

Package Includes

DisplayPort Monitor Cable - 20-ft.
 (6.09 m)

Features

- The future standard for Digital Video and Audio connections
- Supports Displayport v1.1
- Supports Ultra High Definition (UHD) 4K x 2K video resolutions up to 3840 x 2160 @ 30Hz, including 1080p
- Monitor Resolution Support: 3840 x 2160 @ 30Hz, 2560x1600 @ 60Hz, 1920x1200 @ 120Hz
- Supports High Definition Content Protection (HDCP)

Specifications

OVERVIEW	
UPC Code	037332176561
Product Type	Passive
Technology	DisplayPort
VIDEO	
Max Supported Video Resolution	3840 x 2160 @30Hz
Max Supported Color Depth	24-bit True Color
Chroma Sub Sampling	4:4:4
PHYSICAL	
Color	Black
Cable Length (ft.)	20



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (m)	6.1
Shipping Dimensions (hwd / cm)	33.02 x 25.40 x 1.27
Shipping Dimensions (hwd / in.)	13.00 x 10.00 x 0.50
Shipping Weight (kg)	0.28
Shipping Weight (lbs.)	0.62
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	DISPLAYPORT (MALE)
Latching Connector	Yes
FEATURES & SPECIFICATIONS	
Displayport Specification	1.1
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>