

**EK EKOE 180 T**



Sample photo

**Order symbol:** EKOE 180 T  
**Product nbr:** 2538140  
**Description:** Enclosure, PC  
**Remarks:** Transparent cover

**EAN:** 6418074013842  
**EI. number:**  
 Finland: 3425469  
 Electric No. Italy: 7502140  
 Electric No. Sweden: 2538140

Including: Flanged Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	280	280	180	EKO 30-G	Cover
inch:	11.0	11.0	7.1	EKO 80-G	Cover
<b>Materials:</b>				EKO 30-T	Cover
<b>Material:</b>	Polycarbonate			EKO 80-T	Cover
<b>Base colour:</b>	RAL 7035 -light grey			EKOVT	Mounting plate
<b>Cover screws material:</b>	Polyamide			EKOXT	Mounting plate isolated
<b>Cover colour:</b>	Clear transparent			EKV 22	DIN-35 Mounting rail
<b>Cover screws colour:</b>	Grey			EKOZR	Extension frame
<b>Gasket material:</b>	Polyurethane			<b>Rating:</b>	
<b>Temperatures:</b>				Ingress Protection (EN 60529): IP66/IP67	
<b>Temperature °C (short term):</b>	-40 ... 120 °C			Impact Resistance (EN 62262): IK08	
<b>Temperature °C (continuous):</b>	-40 ... 80 °C			Electrical insulation: Totally insulated	
<b>Temperature °F (short term):</b>	-40 ... 250 °F			Halogen free (DIN/VDE 0472, Part 815): 1	
<b>Temperature °F (continuous):</b>	-40 ... 175 °F			UV resistance: UL 508	
<b>Accessories:</b>				Flammability Rating: UL 746C 5"	
EKOE	Base, PC			Glow Wire Test (IEC 695-2-1) °C: 960	
<b>Certificates:</b>				NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12	
				SGS Fimko	
				Gost R	

