
5 CONTACTS BLUE MALE HOUSING (ONLY FOR BOARD MOUNT CONTACTS)




TOLERANCE UNLESS OTHERWISE SPECIFIED		
.X	±0.38	
.XX	±0.25	
.XXX	±0.13	


THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.



ORIGINAL (1)







NOTE:

ELECTRICAL SPECIFICATIONS:


VOLTAGE RATING: 250V MAX. CURRENT RATING: 3A per CONTACT CONTACT RESISTANCE: $15m\Omega$ MAX. INSULATOR RESISTANCE: $1000M\Omega$ min. DIELECTRIC WITHSTANDING VOLTAGE: 1000V AC(RMS) OPERATING TEMPERATURE: -40 °C ~ 105 °C

MATERIAL & FINISH:

HOUSING: PBT WITH GLASS, UL94V-0 CONTACTS: BRASS, TIN PLATED SEALS: SILICONE RUBBER

560 SERIES WATERPROOF CONNECTOR







THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC.,AND
SHALL NOT BE REPRODUCED, OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

ACAD REFERENCE NO.: 560 Assembly				
DRAWN: C.B	DATE: July 23, 2020			
CHECKED:	DATE:			
SCALE: 2:1	SHEET 1 OF 1			

DRAWING NUMBER:	560 Assembly	ISSUE
PART NUMBER:	560-005-420-301	1