



THIS IS A C.A.D. GENERATED DRAWING DO NOT MAKE MANUAL REVISIONS TO MASTER.




ISSUE NUMBER ORIGINAL

(1)







NOTES:

MATERIAL: HOUSING: SHELL: CONTACT: **O-RING:**


PBT, **UL94V-0** STEEL, NICKEL PLATED COPPER ALLOY, GOLD FLASH PLATED SILICONE

OPERATING TEMPERATURE: -25°C TO 85°C

CURRENT RATING: CONTACT RESISTANCE: **INSULATOR RESISTANCE:** DIELECTRIC WITHSTANDING VOLTAGE: **3A PER CONTACT** 10mΩ MAX. 5000MΩ min.

1000V AC rms

633W SERIES D-SUB CONNECTOR		SW REFERENCE NO.: 633W ASSEMBLY				
		DRAWN: C.B		DATE: AUG. 01/2018		18
		CHECKED:		DATE:		
EDAC INC TORONTO, ONTARIO CONNECTION TO QUALITY & SERVICE	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INC.,AND SHALL NOT BE REPRODUCED,OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	SCALE: 1:1		SHEET 1	OF	1
		DRAWING NUMBER:	633-W15-262-012			ISSUE
		PART NUMBER:	633-W15-	262-012		1





THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES 2011/65/EU FOR RoHS COMPLIANCY.

