

FEATURES

- IP67 Rated
- Halogen free
- Voltage ratings of 230V and 415V offered in this range
- All models offered in the range are highly reliable and excellent quality
- Straight body orientation
- Red, yellow and blue colours offered in this range of power connectors
- Conforms to the latest requirements of British and European standards
- Screw terminals accept conductors upto 2.5mm² for 16A, 6mm² for 32A, 16mm² for 63A and 50mm² for 125A types

RS PRO IP67 Red Cable Mount 3P+N+E Industrial Power Plug, Rated At 63.0A, 415.0 V

RS Stock No.: 724-9145



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From the trusted brand RS PRO, comes a range of high-quality cable mounted free socket power connectors. Manufactured to industry standards these connectors are easy to assemble and are a fantastic industrial plug solution for powering tools and machinery at a range of different voltage requirements.

General Specifications

Syntetical Description	Plug
Pole Format	3P+N+E
Hour Position	6h
Gender	Male
Body Orientation	Straight
Material	Engineering Plastic
Colour	Red
Applications	Providing power for machinery on construction sites, Woodworking machines, Maintenance workshops in the light industry

Electrical Specifications

Current Rating	63A
Voltage Rating	346-415V
Working Frequency	50Hz, 60Hz
Plug/Socket	Plug
Termination Method	Screw
Cable CSA	16.0mm ²
Contact Material	Nickel plated brass

Mechanical Specifications

Mounting Type	Cable Mount
----------------------	-------------

Protection Category

IP Rating

IP67

Approvals

Compliance/Certifications

EN 60309-1, EN 60309-2



