

# Technical data sheet

## Set made of Quick clip and Quick pipe

Item no. 2154528



Convenient set consisting of Quick clip and Quick pipe.

The Quick pipe combines the advantages of cable duct and installation pipe into an intelligent system. This system allows tidy and safe surface-mounted installation of all kinds of cables on walls and ceilings. Quick pipe is available in four metric sizes: M16, M20, M25 and M32 and the stock length is 2 m.

The system is VDE-tested and achieves a protection rating of IP44. The Quick pipe can be used in the temperature range from -25 to +60 °C and is resistant to an impact energy of 5 J.




**PVC** Polyvinylchloride

### Master data

Item no.	2154528
Type	2954 M20 LGR
Description 1	Quick-Pipe set
Description 2	Quick trunking + Quick clip
Dimension	M20
Colour	Light grey
RAL number	7035
Material	Polyvinylchloride
Material symbol	PVC
Smallest sales unit (VG)	1 Piece
Weight	508,00 kg/100 pc.

### Technical data



Dimension C	10 mm
Dimension D	20,00 mm
Dimension M	17
Dimension t	1,50 mm
Surface-mounted	<input checked="" type="checkbox"/>
Flame-resistant version	<input type="checkbox"/>
Concrete installation	<input checked="" type="checkbox"/>
Size	M20
Halogen-free	<input type="checkbox"/>
Installation on wood	<input checked="" type="checkbox"/>
Installation under the ground	<input type="checkbox"/>
Installation outdoors	<input type="checkbox"/>
Machines and system installation	<input checked="" type="checkbox"/>
With sleeve	<input type="checkbox"/>
Temperature range	-25+60 °C
Quick pipe	40,00 m
Quick clip	120,00 pc.
Set consisting of	40 m Quick pipe and 120x OBO Quick clip
Underfloor installation (screed)	<input type="checkbox"/>
Concealed	<input type="checkbox"/>

### Classification for electrical pipe standards