





Model Number:	55-2954	
GENERAL SPECIFICATIONS		
Nominal Diameter:	18 inch	
Rated Impedance:	8 ohms	
Operating Bandwidth:	27Hz ~ 3KHz	
Power Handling Capacity:	300W RMS	
Sensitivity (1W/M):	100 dB	
Voice Coil Diameter:	4 inch	
THIELE-SMALL PARAMETER		
Resonance Frequency	Fs:	27 Hz
DC Resistance	Re:	7.2 ohm
Mechanical Q Factor	Qms:	2.5
Electrical Q Factor	Qes:	0.324
Total Q Factor	Qts:	0.29
Equivalent Cas air load	Vas:	224 liters
Coil Inductance	Le:	1.69mH
Efficiency Bandwidth Product	EBP	83.33
Voice Coil Over Hang	X-max	4.0mm
PHYSICAL INFORMATION		
Basket:	Stamped Steel	
Magnet Type:	125 OZ	
Cone Material:	None press paper	
Surround:	cloth	
Dust Cap:	paper	
Damper:	cloth	





ALL DIMENSIONS ARE IN MILLIMETERS