



# HG 330-S

Hot-air blower



simple.  
good.  
affordable.

# HG 330-S: The multifunctional Weldy hot-air blower

The Weldy HG 330-S hot-air blower is a high-performance hot-air gun. Thanks to quick, infinitely variable temperature adjustment from 80 °C to 600 °C and a two-stage blower, the HG 330-S is great for professional and home improvement jobs alike. Whether for paint or varnish removal, mounting and shrinking plastic films, refreshing plastic parts with hot air, or defrosting pipes, the HG 330-S hot-air hand tool makes tasks that require hot air easier thanks to high heat and blowing strength coupled with low weight and ergonomic design.

Hot-air blower

## HG 330-S

- can be used for multiple functions
- quick, infinitely variable temperature adjustment
- integrated two-stage blower
- high heat and blowing performance



### Technical data

Voltage	V~	100	120	230
Max. power	W	1200	1400	2000
Temperature	°C	80 - 600	80 - 600	80 - 600
Air volume	l/min	250 / 450	250 / 450	250 / 550
Dimensions L × W × H	mm	250 × 80 × 230		
Weight	kg	0.7		
Conformity marking		CE		
Protection class II		□		

Only available as a kit (hot-air hand tool incl. accessories)



**Kit HG 330-S**

230 V / 2000 W, CN plug	124.404
230 V / 2000 W, EU plug	164.324
230 V / 2000 W, CH plug	134.691
230 V / 2000 W, UK plug	131.322
230 V / 2000 W, AUS plug	133.772
120 V / 1400 W, US plug, polarized (UL)	123.156
100 V / 1200 W, JP plug	120.129

**Accessories (included in kit)**

119.341 Glass protection nozzle	•
119.343 Tubular nozzle Ø 20 mm	•
119.344 Spoon reflector	•
Carton tool packaging	•
Instruction manual	•



Händleradresse:

