

FL MGUARD RS2005 TX VPN - Router



2701875

<https://www.phoenixcontact.com/us/products/2701875>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

Remote maintenance router, 10/100 Mbps, NAT, VPN, firewall, Unmanaged 5-port Switch



Your advantages

- Central management tool
- Maximum performance
- Maximum security

Commercial Data

Item number	2701875
Packing unit	1 pc
Minimum order quantity	1 pc
Sales Key	DN28
Product Key	DNN331
Catalog Page	Page 336 (C-6-2019)
GTIN	4046356869324
Weight per Piece (including packing)	902.5 g
Weight per Piece (excluding packing)	902 g
Customs tariff number	85176200
Country of origin	DE

Technical Data

Dimensions

Width	45 mm
Height	130 mm
Depth	120.6 mm

Material specifications

Color	silver
Housing material	Metal

Interfaces

Ethernet

Connection method	RJ45
Transmission speed	10/100 Mbps
Transmission physics	Ethernet in RJ45 twisted pair
Transmission length	100 m (per segment)
Signal LEDs	Supply voltage, data transmission, error, link, activity
No. of channels	6 (RJ45 ports)

Signal contact

Connection method	Plug-in/screw connection via COMBICON
Additional text	not electrically isolated

VPN - release button

Connection method	24 V DC/250 mA can be connected as an option
-------------------	--

System properties

Functionality

Basic functions	Router with firewall and VPN for 2 tunnels, integrated 5-port switch, metal housing, slot for SD memory card, extended temperature range, high-performance firewall/VPN: up to 124 Mbps/40 Mbps
-----------------	---

System requirements

Supported browsers	HTTPS support required
--------------------	------------------------

Product properties

Type	Stand-Alone
Product type	Security router for the DIN rail

Insulation characteristics

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Security functions

1:1 Network Address Translation (NAT) in the VPN	Supported
--	-----------

Number of VPN tunnels	2
Authentication	X.509v3 certificates with RSA or PSK
Data integrity	MD5, SHA-1, SHA 256, SHA-512
Dynamic Host Configuration Protocol (DHCP) support	Server or Relay Agent
Filtering	Incoming or outgoing traffic
Firewall data throughput	max. 130 Mbps (Router mode, default firewall rules, bidirectional throughput)
	max. 61 Mbps (Stealth mode, default firewall rules, bidirectional throughput)
Firewall rules	simple stateful inspection firewall, no user firewall, no conditional firewall, no rule sets
Basic functions	Router with firewall and VPN for 2 tunnels, integrated 5-port switch, metal housing, slot for SD memory card, extended temperature range, high-performance firewall/VPN: up to 124 Mbps/40 Mbps
Internet Protocol Security (IPsec) mode	ESP tunnel / ESP transport
Link Layer Discovery Protocol (LLDP)	As per protocol 802.2
Network Time Protocol (NTP) client	Client
Remote Syslog Logging	On external server
Routing	Standard routing, NAT, 1:1-NAT, port forwarding
Encryption methods	DES, 3DES, AES-128, -192, -256
Virtual private network (VPN) throughput	max. 40 Mbps (Router mode, VPN bidirectional throughput)
	max. 27 Mbps (Stealth mode, VPN bidirectional throughput)

Electrical properties

Local diagnostics	P1, P2 Supply voltage US1, US2 Green LED
	One LED per port Link active Green LED

Supply

Supply voltage (DC)	24 V DC (redundant)
Supply voltage range	11 V DC ... 36 V DC
Power supply connection	Via COMBICON, max. conductor cross section 2.5 mm ²
Residual ripple	3.6 V _{PP} (within the permitted voltage range)
Max. current consumption	180 mA (unloaded outputs)
Typical current consumption	100 mA (at U _S = 24 V DC)

Function

Signal contact control voltage	24 V DC (typical)
Signal contact control current	250 mA (short-circuit-proof)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)

2701875

<https://www.phoenixcontact.com/us/products/2701875>

Approvals

Conformity/Approvals

Conformance

CE-compliant

Mounting

Mounting type

DIN rail mounting

EMC data

Electromagnetic compatibility

Conformance with EMC Directive 2014/30/EU

Signaling

Status display

LEDs:P1, P2, Fault, State, Error, LAN, WAN

FL MGUARD RS2005 TX VPN - Router



2701875

<https://www.phoenixcontact.com/us/products/2701875>

Approvals



EAC

Approval ID: RU*DE*08.B.00731/19



UL Listed

Approval ID: FILE E 238705



cUL Listed

Approval ID: FILE E 238705

FL MGUARD RS2005 TX VPN - Router



2701875

<https://www.phoenixcontact.com/us/products/2701875>

Classifications

ECLASS

ECLASS-11.0	19170406
ECLASS-12.0	19170406
ECLASS-13.0	19170406

ETIM

ETIM 8.0	EC001478
----------	----------

UNSPSC

UNSPSC 21.0	43222600
-------------	----------

FL MGuard RS2005 TX VPN - Router



2701875

<https://www.phoenixcontact.com/us/products/2701875>

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

FL MGUARD RS2005 TX VPN - Router



2701875

<https://www.phoenixcontact.com/us/products/2701875>

Accessories

FL CAT5 PATCH 0,3 - Patch cable

2832250

<https://www.phoenixcontact.com/us/products/2832250>

Patch cable, CAT5, assembled, 0.3 m



FL CAT5 PATCH 0,5 - Patch cable

2832263

<https://www.phoenixcontact.com/us/products/2832263>

Patch cable, CAT5, assembled, 0.5 m



FL MGUARD RS2005 TX VPN - Router

2701875

<https://www.phoenixcontact.com/us/products/2701875>



FL CAT5 PATCH 1,0 - Patch cable

2832276

<https://www.phoenixcontact.com/us/products/2832276>

Patch cable, CAT5, assembled, 1 m



FL CAT5 PATCH 1,5 - Patch cable

2832221

<https://www.phoenixcontact.com/us/products/2832221>

Patch cable, CAT5, assembled, 1.5 m



FL MGUARD RS2005 TX VPN - Router

2701875

<https://www.phoenixcontact.com/us/products/2701875>



FL CAT5 PATCH 2,0 - Patch cable

2832289

<https://www.phoenixcontact.com/us/products/2832289>

Patch cable, CAT5, assembled, 2 m



FL CAT5 PATCH 3,0 - Patch cable

2832292

<https://www.phoenixcontact.com/us/products/2832292>

Patch cable, CAT5, assembled, 3 m



FL MGUARD RS2005 TX VPN - Router

2701875

<https://www.phoenixcontact.com/us/products/2701875>



FL CAT5 PATCH 5,0 - Patch cable

2832580

<https://www.phoenixcontact.com/us/products/2832580>

Patch cable, CAT5, assembled, 5 m



FL CAT5 PATCH 7,5 - Patch cable

2832616

<https://www.phoenixcontact.com/us/products/2832616>

Patch cable, CAT5, assembled, 7.5 m



FL MGUARD RS2005 TX VPN - Router

2701875

<https://www.phoenixcontact.com/us/products/2701875>



FL CAT5 PATCH 10,0 - Patch cable

2832629

<https://www.phoenixcontact.com/us/products/2832629>




Patch cable, CAT5, assembled, 10 m

FL CAT6 PATCH 12,5 - Patch cable

2891369

<https://www.phoenixcontact.com/us/products/2891369>



Patch cable, CAT6, pre-assembled, 12.5 m

FL MGUARD RS2005 TX VPN - Router

2701875

<https://www.phoenixcontact.com/us/products/2701875>



FL CAT6 PATCH 15,0 - Patch cable

2891372

<https://www.phoenixcontact.com/us/products/2891372>



Patch cable, CAT6, pre-assembled, 15.0 m

FL CAT6 PATCH 20,0 - Patch cable

2891576

<https://www.phoenixcontact.com/us/products/2891576>



Patch cable, CAT6, pre-assembled, 20.0 m

FL MGUARD RS2005 TX VPN - Router

2701875


<https://www.phoenixcontact.com/us/products/2701875>



FL RJ45 PROTECT CAP - Dust protection

2832991

<https://www.phoenixcontact.com/us/products/2832991>



Dust protection caps for RJ45 socket

FL PLUG RJ45 GR/2 - RJ45 connector

2744856

<https://www.phoenixcontact.com/us/products/2744856>



RJ45 connector, design: RJ45, degree of protection: IP20, number of positions: 8, 1 Gbps, CAT5 (IEC 11801:2002), material: Plastic, connection method: Crimp connection, cable outlet: straight, color: green, Ethernet

FL MGUARD RS2005 TX VPN - Router




2701875

<https://www.phoenixcontact.com/us/products/2701875>

FL PLUG RJ45 GN/2 - RJ45 connector

2744571

<https://www.phoenixcontact.com/us/products/2744571>



RJ45 connector, design: RJ45, degree of protection: IP20, number of positions: 8, 1 Gbps, CAT5 (IEC 11801:2002), material: Plastic, connection method: Crimp connection, cable outlet: straight, color: green, Ethernet

FL CRIMPTOOL - Assembly tool

2744869

<https://www.phoenixcontact.com/us/products/2744869>



Crimping pliers, for assembling the RJ45 plugs FL PLUG RJ45..., for assembly on site

FL MGuard RS2005 TX VPN - Router

2701875

<https://www.phoenixcontact.com/us/products/2701875>



FL MGuard LIC FW MNT 2030 - License

1493074

<https://www.phoenixcontact.com/us/products/1493074>



License for firmware maintenance until 2030

MGuard Secure VPN Client LIC - License

2702579

<https://www.phoenixcontact.com/us/products/2702579>



License for mGuard Secure VPN Client v11.x

FL MGUARD RS2005 TX VPN - Router

2701875


<https://www.phoenixcontact.com/us/products/2701875>



FL MGUARD DM UNLIMITED - Software

2981974

<https://www.phoenixcontact.com/us/products/2981974>



Central device management software for MGUARD devices for any number of devices in the field. For installation on a PC. No additional licenses required. Download trial version for up to 10 devices.

SD FLASH 2GB - Program / configuration memory

2988162

<https://www.phoenixcontact.com/us/products/2988162>



Program and configuration memory, for extending the internal flash memory, pluggable, 2 GB.

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com