



Click [here](#) for the 3D model.

Dimensions

L	17mm +/-0.5mm
W	17.1mm +/-0.5mm
T	4mm MAX
LL	2.1mm NOM
G	11.9mm NOM

Packaging Specifications

Packaging	T&R, 330mm
Packaging Quantity	100

General Information

Series	MPXV
Style	SMD
Chip Size	1740(6868)
Description	Surface Mount Inductor
Features	Power Inductors
RoHS	Yes
Qualifications	AEC-Q200
AEC-Q200	Yes
Core	Composite
Miscellaneous	40 (K) Temperature Rise Max.

Specifications

Inductance	10 uH
Inductance Tolerance	20%
Temperature Range	-55/+155°C
Shielded	Yes
Current	9.5 A (Irms, 40C Rise By Self Heating), 10 A (Isat, 20% Drop In Inductance), 14.5 A (Isat, 30% Drop In Inductance)
DC Resistance	21.7 mOhms
Self-Resonant Frequency	6.8 MHz