

Dławiki PG IP67 i metryczne MG IP67

PG cable glands IP67 and MG metric cable glands IP67


IP67

Dławiki PG IP67 / PG cable glands IP67

| Numer katalogowy | Typ Type | Ø montażu Ø assembly | D1 | D2 | B1 | L1 | L2 | L3 | Ø przewodu Wire diameter | Klucz / Spanner | Norma Norm | Opakowanie : sztuk Quantity in package |
|------------------|----------|-------------------------|------|-------|------|------|------|------|-----------------------------|-----------------|------------|---|
| Catalogue number | [-] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [-] | [-] |
| D.3070 | PG-7 | 12,5 | 11,7 | 8,5 | 6 | 8 | 14,5 | 14,3 | 3,5 - 6,0 | 16 / 18 | DIN 40430 | 50 |
| D.3071 | PG-9 | 15,2 | 14 | 11 | 8,5 | 8,1 | 16,5 | 15,3 | 6,0 - 8,0 | 18 / 22 | DIN 40430 | 50 |
| D.3072 | PG-11 | 18,3 | 17,6 | 14,20 | 9,6 | 8,5 | 16,5 | 16,8 | 8,0 - 10,0 | 22 / 24 | DIN 40430 | 50 |
| D.3073 | PG-13,5 | 19,5 | 18,5 | 15,2 | 12,2 | 8,6 | 17,5 | 19,5 | 10,0 - 12,0 | 24 / 26 | DIN 40430 | 50 |
| D.3074 | PG-16 | 22,5 | 21,2 | 17,2 | 14,5 | 10 | 17,5 | 18,1 | 12,0 - 14,0 | 26 / 30 | DIN 40430 | 50 |
| D.3075 | PG-21 | 28,2 | 27,1 | 22 | 18,5 | 11 | 19,5 | 23,5 | 14,0 - 18,0 | 32 / 36 | DIN 40430 | 50 |
| D.3076 | PG-29 | 37,2 | 35,9 | 30,6 | 25,5 | 11,5 | 23 | 25,5 | 18,0 - 25,0 | 42 / 45 | DIN 40430 | 10 |
| D.3077 | PG-36 | 47,2 | 45,8 | 38,9 | 33,3 | 14,4 | 25 | 29,5 | 25,0 - 32,0 | 51 / 58 | DIN 40430 | 10 |
| D.3078 | PG-42 | 53,9 | 52,2 | 46,5 | 39,6 | 15,2 | 26,5 | 30,5 | 32,0 - 38,0 | 60 / 64 | DIN 40430 | 10 |
| D.3079 | PG-48 | 59,3 | 58,2 | 49,0 | 45,1 | 15,2 | 27,0 | 30,0 | 38,0 - 44,0 | 64 / 68 | DIN 40430 | 10 |

Dławiki metryczne MG IP67 / MG metric cable glands IP67

| Numer katalogowy | Typ Type | Ø montażu Ø assembly | D1 | D2 | B1 | L1 | L2 | L3 | Ø przewodu Wire diameter | Klucz / Spanner | Norma Norm | Opakowanie : sztuk Quantity in package |
|------------------|----------|-------------------------|------|------|------|------|------|------|-----------------------------|-----------------|-------------|---|
| Catalogue number | [-] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [mm] | [-] | [-] |
| D.3088 | M12 | 12 | 10 | 8 | 6 | 7,5 | 14,7 | 15,5 | 3,0 - 6,5 | 16 / 18 | PN-EN 50262 | 25 |
| D.3089 | M16 | 16 | 14,3 | 10,7 | 8 | 7,5 | 14,7 | 15,3 | 6,5 - 8,0 | 19 / 22 | PN-EN 50262 | 50 |
| D.3080 | M20 | 20 | 18,5 | 14,7 | 12 | 9,5 | 17 | 18,2 | 8,0 - 12,0 | 24 / 27 | PN-EN 50262 | 25 |
| D.3081 | M25 | 25 | 23,3 | 19 | 18 | 10 | 20 | 23,5 | 12,0 - 18,0 | 32 / 32 | PN-EN 50262 | 25 |
| D.3082 | M32 | 32 | 30,4 | 24 | 25 | 11 | 20 | 21,5 | 18,0 - 24,0 | 36 / 38 | PN-EN 50262 | 10 |
| D.3083 | M40 | 40 | 38,1 | 33 | 32 | 15 | 17 | 29,5 | 24,0 - 32,0 | 51 / 50 | PN-EN 50262 | 10 |
| D.3090 | M50 | 50 | 38 | 38 | 40 | 14 | 24 | 32,5 | 32,0 - 38,0 | 60 / 68 | PN-EN 50262 | 10 |
| D.3091 | M63 | 63 | 61,7 | 54 | 45 | 14 | 35 | 40,5 | 38,0 - 45,0 | 70 / 76 | PN-EN 50262 | 10 |



Dławiki gumowe PG / PG rubber cable glands

| Numer katalogowy | Typ Type | Ø montażu Ø assembly | Norma Norm | Opakowanie : sztuk Quantity in package |
|------------------|----------|-------------------------|------------|---|
| Catalogue number | [-] | [mm] | [-] | [-] |
| D.3410 | PG-13,5 | 20,5 | DIN 40430 | 1 |
| D.3411 | PG-16 | 22 | DIN 40430 | 1 |
| D.3412 | PG-21 | 29 | DIN 40430 | 1 |
| D.3413 | PG-29 | 37 | DIN 40430 | 1 |

