

COAXIAL CONNECTOR, MMCX, 50 Ohm, Straight cable plug (male)

11_MMCX-50-1-1/111_O

Properties

- Very small size
- Easy to connect and disconnect
- Wide range of board connectors and cable connectors available



Product configuration		
Interface type	Standard	
MMCX	HUBER+SUHNER-MMCX	
Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	
Crimp ferrule	Brass	Gold Plating (without Nickel underplating)
Electrical data		
Impedance	50 Ω	
Interface frequency	6 GHz	
Mechanical data		
Weight	0.0009 kg	
Mating cycles	500	
Cable entry centre contact	crimped	
Cable entry outer contact	crimped	
Environmental data		
Operation temperature	-55 °C ... 155 °C	

COAXIAL CONNECTOR, MMCX, 50 Ohm, Straight cable plug (male)

11_MMCX-50-1-1/111_O

Ordering Information Table	
Item number	Item description
22645298	11_MMCX-50-1-1/111_OE
22651666	11_MMCX-50-1-1/111_OH

Suitable cables	
Cable group	U1 - 1 mm / 50 Ohm

Additional Information	
Only as assembly	No

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P31309 / Date of publication: 01.12.2023 / uncontrolled copy