








Crocodile clips

AK 2 B 2540 I



Product	AK 2 B 2540 I
description	Contact-protected, high-strength, wide-opening alligator clip. Clamping range up to 30mm bolt diameter. Solid wire clip, U-shaped and fine wire section. Nickel-plated brass connecting socket, pluggable with 4mm safety measuring leads.
operating instruction	BA465
article-no. / *colour	9724051xx <div style="display: flex; justify-content: space-around; align-items: center;"> <div style="text-align: center;"> 00 black</div> <div style="text-align: center;"> 01 red</div> <div style="text-align: center;"> 02 blue</div> <div style="text-align: center;"> 03 yellow</div> <div style="text-align: center;"> 04 green</div> <div style="text-align: center;"> 88 yellow green</div> </div> <div style="text-align: right; margin-top: 5px;">Ni</div>
drawing	
technical data	
connection	unsprung socket 4 mm
rated voltage	AC/DC 1000 V
measurement cat. acc. to IEC 61010	CAT II
rated current (consider derating curve)	32 A
material socket	brass, nickel plated
housing material	PP
temperature range acc. To IEC61010 ⁽¹⁾	-30 °C to +70 °C
inflammability class acc. to UL 94 (only valid for basic material of housing)	HB

4 mm safety system

clamping range	30 mm
----------------	-------

⁽¹⁾ contact the manufacturer for applications at deviating temperature ranges
stand: 13.02.2023

stand: 13.02.2023