

KradeX



www.DIP8.ru

Kradex

3

4

5

6

7

8

9

10

3D,

DIN-

9

11



Kradex

1985

2000



(PS)

ABS

13

20 000



(), PC ABS, Noryl).



(1000 2,

3000 3)

24





186

15x17x26

95x190x280

	Z-7AP/BK	Z-23/J	Z-29	Z-30A	Z-34A/J	Z-43	Z-44/J	Z-45/JW	Z-47	Z-52/J
[mm]	31,5	30	28	44	28	16	33	43	20	40
[mm]	55	59	93	70	68	31	80	55	40	74
[mm]	106	84	126	120	129	46	149	100	50	145
	Z-53/J	Z-63	Z-66/J	Z-70U	Z-73	Z-76	Z-80	Z-91/J	Z-94/JW	Z-115/J
[mm]	22	15	65	28	32	28	38	36	26,5	21,5
[mm]	65	17	79	59	79	59,5	90	100	46,5	30
[mm]	90	26	130	76	109	109	120	130	65,5	105



72

30x62x69

118x297x216

	Z-1A/JW	Z-3/JW	Z-5A	Z-6/J	Z-18	Z-19/J	Z-26/J	Z-36/J	Z-40
[mm]	70	70	49	39	65	25	60	42	74
[mm]	188	150	90	91	76	94	220	66	100
[mm]	197	110	110	66	176	128	220	125	180
	Z-50A	Z-67/J	Z-97/J	Z-98/J	Z-99/J	Z-112F/J	Z-112A	Z-112BF/J	Z-112AF/J
[mm]	36	29	31,1	40,15	51,54	60	40	80	40
[mm]	91	63	60,66	60,66	60,66	136	136	136	136
[mm]	146	67	120,76	120,76	120,76	185,5	185,5	185,5	185,5

DIN-

Z-100



Z-101



Z-102



Z-103



Z-104



Z-105



Z-106



Z-107F



Z-108



Z-109F



KM-110F



KM-71



DIN -	ABS	ABS VO (38	DIN -	-
	62x88x34	62x88x136/65x89x107			

DIN-

	Z-100	Z-101	Z-102	Z-103	Z-104	Z-105
[mm]	64,6	65,6	65,2	62,8	62,8	64,9
[mm]	89	89	89,4	88,8	88,8	90
[mm]	69,8	107	53	34	138	17,5
[]	4	6	3	2	8	1
	Z-106	Z-107F	Z-108	Z-109F	Z-110F	KM-71
[mm]	65	65	65	65,1	65,3	70
[mm]	90	90	90	90	90	91
[mm]	35	52,5	70	87,5	105	105
[]	2	3	4	5	6	6



26

32x60x84

63x69x114/45x70x120

	Z-10	Z-10A	Z-13	Z-13A	Z-16	Z-21	Z-27	Z-30	Z-31	Z-35
[mm]	52	46	37	40	63	55	46	46	44	52
[mm]	58	53	47	48	70	64	70	70	70	62
[mm]	72	81	65	72	114	82	120	120	120	85
	Z-42	Z-64	Z-66	Z-92	Z-92U	KM-403	KM-404	KM-67	KM-68	KM-104
[mm]	46	57	65	32	32	88	65	67	70	45
[mm]	56	65	79	60,5	77	50	70	97	110	71
[mm]	83	89	130	85	85	118	125	137	187	114



				70				ABS.	
IP55	IP65.	30x40x64	150x200x360						

	Z-46AH	Z-54/JH	Z-56/JH	Z-57/JH	Z-58/JH	Z-59/JH	Z-65/JH	Z-74/JH
[mm]	73	41	42	55	55	58	30	56
[mm]	144	74	64	78	82	115	40	125
[mm]	198	89	88	118	158	125	64	176
	Z-90/JH	Z-95/JH	Z-96/JH	Z-116/JH	Z-117/JH	Z-111/JH	KM-500	TH-208
[mm]	80	95	36,5	36	37	55	49	35,3
[mm]	175	190	50	49	57	80	133	36,5
[mm]	225	280	70	51	63	82	133	184,5



ABS.

12x30x60 25x69x142

	Z-14	Z-14A	Z-14B	KMp5	KMp7	KMp9	KMp11	KMp14N	KMp15N	KMp18	KMp18K
[mm]	22	13	16	12	14	14	10	16	16	13	13
[mm]	49	31	38	40	37	33	29	38	38	35	35
[mm]	150	61	56	50	62	55,5	62	65	65	50	50

9



9 9

25x69x142 39x81x145

ABS.

9

	Z-32	Z-32A	Z-48	Z-49	Z-55	Z-62	Z-89F
[mm]	27	26	35	35	28	29	25
[mm]	65	59	80	80	63	63	68,5
[mm]	110	188	145	145	104	83	141,5



3D



3D-



<http://DIP8.ru>

 2015

ВРЕМЯ ИМЕТЬ **КОРПУС**

KradeX



ООО "Айтекс"

Электронные компоненты, оборудование и материалы

Офис-склад: г. Москва, 1-й Варшавский пр-д, д. 2, стр. 8, оф. 107

Прием заказов: 8-800-555-84-55, info@dip8.ru

www.itecs.ru

www.DIP8.ru