


MAGNETIC BUZZER


Material of Case: ABS
 Colour: Black
 Operating Temperature: -20°C +60°C
 Storage Temperature: -30°C +70°C

DIMENSIONS (in mm)

Leadwire Type




Top View




Side View


Pin Type



Top View



Side View



Electrical Specifications

Model No.	2S3030	2S3060	2S3090	2S3120	2S3240	2S3415	2P3015	2P3030	2P3060	2P3090	2P3120	2P3240	2D3060	2D3090	2D3120
Operating Voltage	2-5	4-9	6-11	9-15	15-28	4-15	1-3	2-5	4-9	6-11	8-15	15-28	4-9	6-11	8-15
Rated Voltage (VDC)	3	6	9	12	24	12	1.5	3	6	9	12	24	6	9	12
Max. Current at Rated Voltage (mA)	35	35	40	40	25	15	5	8	10	10	15	20	35/10	35/15	40/15
Frequency (KHz)	2.8±0.2	2.8±0.2	2.8±0.2	2.8±0.2	2.8±0.2	2.8±0.2	2.8±0.2	2.8±0.2	2.8±0.2	2.8±0.2	2.8±0.2	2.8±0.2	2.8±0.2	2.8±0.2	2.8±0.2
Min. Sound Pressure at Rated Voltage (dBA/30cm)	85	90	90	95	95	90	70	73	78	80	85	85	85/70	85/75	90/80
Tone	SINGLE	SINGLE	SINGLE	SINGLE	SINGLE	SINGLE	PULSE	PULSE	PULSE	PULSE	PULSE	PULSE	SINGLE/PULSE	SINGLE/PULSE	SINGLE/PULSE
Pulse Rate at Rated Voltage (Pulse/Sec)	NIL	NIL	NIL	NIL	NIL	NIL	2-7	2-7	2-7	2-7	2-7	2-7	2-7	2-7	2-7
Terminal	LEAD/PIN	LEAD/PIN	LEAD/PIN	LEAD/PIN	LEAD/PIN	LEAD/PIN	LEAD/PIN	LEAD/PIN	LEAD/PIN	LEAD/PIN	LEAD/PIN	LEAD/PIN	3 LEADS	3 LEADS	3 LEADS