


DC Power Plugs


171-3215-EX, 171-3216-EX











Dimensions: mm (in.)

SPECIFICATIONS	
Type:	right angle DC power solder terminal
Right angle application:	2.1±0.1mm (171-3215)-EX
	2.5±0.05mm (171-3216)-EX
Max. Cable Size:	24 Awg
Contact resistance:	50mΩ max.
Insulation resistance:	100MΩ min.
Breakdown voltage:	500VAC
DC power & temperature rating:	12VDC 0.5A
Color:	Black
Lug Hole Size:	0.9mm-1mm dia.
Contacts A, B, & terminal:	Nickel Plated Brass
Insulator:	ABS
Cap:	PVC
Operating temperature:	-25°C ~ +70°C
RoHS Compliant by Exemption	

Date Last Revised: 10-15-14

Available from Mouser Electronics 1-800-346-6873 / www.mouser.com KC-300907

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kobiconn:

171-3216-EX 171-3215-EX