

Art.-No.	VE	PG	EAN
234002010	1	132	

DUOveral Plus, 3=6, all sockets with connection option for one grounding-type plug or two euro-plugs, with illuminated switch (2-pole), with shutter, with 35° turned sockets, 52mm distance between sockets, cable H05VV-F3G1,5mm², 5m, mountable, 16A, 250V~, white



Technical data	234002010
Housing shape	Rectangular
Material	Plastic
Material quality	Thermoplastic
Surface protection	Untreated
Surface finishing	Matt
Colour	White
Degree of protection (IP)	IP20
Angle rotated central insert	35°
Number of socket outlets with protective contact	3
Number of Euro socket outlets	6
Number of CEE socket outlets	0
Number of socket outlets with earth pin	0
Number of cold device socket outlets	0
Residual current circuit breaker (RCCB)	No
Mains filter	No
Number of other socket outlets	0
Over voltage protection	No
Nominal current	16A
Core cross section	1.5mm ²
With cover	No
Transparent	No
Length of power cord	5m
Rotated central insert	Yes