

DL-80K1








Amt:I/P:20A~50A O/P:03A~65A
Terminal:T:250 S:Screw

● COMPONENTS TABLE

Min. Insertion Loss(dB) in 50 ohm system												
Comm. Mode(L-G) in MHz							Diff. Mode(L-L) in MHz					
Amt	0.15	0.5	1	5	10	30	0.15	0.5	1	5	10	30
30A	35	62	55	58	54	22	32	43	47	45	29	26
50A	35	50	52	53	60	32	29	40	39	42	42	27
80A	32	46	57	53	45	29	29	56	58	60	46	24

● SCHEMATIC



● SPECIFICATION

1. Hipot rating (one minute)

Line to Ground : 115 V DC

Line to Ground : 250 V DC

2. Power line frequency : 50/60Hz

3. Rated Voltage : 115/250V AC

5. Operating temp : -25~85°C

● DIMENSIONS (mm)

