

stay connected

M12 Bu. D-cod. / RJ45 Ethernet adapter 90° 4-pol.

Ethernet CAT5 Adapter M12/RJ45 (female/female) 90°, D-coded, 4-pole, shielded

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

Link to Product

Illustration



Product may differ from Image

More Info







_	_	-	-
_	O	r	ш

Form 44681

Technical Data	
Operating voltage	60 V DC
Operating current per contact	max. 1.76 A
Transfer parameters	CAT5, class D (ISO/IEC 11801:2002), (EN 50173-1)
Transfer rate	10/100 Mbit/s full duplex
Protection	IP67 (M12) - IP20 (RJ45)
Locking material	Brass, chrome plated

General data



stay connected

Temperature range	-25+85 °C	
Commercial data		
country of origin	CZ	
customs tariff number	85366990	
minimum order quantity	1	