

# Technical data sheet



Version: A/0

CU520M

USB C/M to C/M Cable with IC 20Gbps USB4 Aluminum shell

## 【Product Picture】



## 【Product Description】

USB C/M to C/M Cable with IC 20Gbps USB4 Aluminum shell

## 【Interface description】

Material: Aluminum shell+Braid+Nickel plated plug

Length:2m

Data transfer: 20Gbps USB4

Current Rating: 5A

Power: Built in E-Marker Chip support 100W

USB Power Delivery :Support

Video: Single 8K@60Hz 5K@60Hz or Dual 4K@60Hz

Function: Charge, Data Transfer, Video, Audio

Compatible with Thunderbolt 3,USB3.2 & 3.1 Transfer protocol

## 【Compatibility Test】

Please make sure that your laptop Type C port support DisplayPort Alt Mode(video output).

Compatibility: MacBook Pro 2019/ 2018, iPad Pro 2018, Mac Mini 2018, iMac 2017, Surface Book 2, Surface Go, Dell XPS 15 & 13 & 12,Lenovo Yoga 920/ Yoga 910/ Yoga 900, HP Spectre x360 13 & 15 inch, Samsung Galaxy S10, S10+, S9, S9+, S8, S8+, LG G5,G7, Q8, HTC 10 HUAWEI P20, HUAWEI Mate 10, and other USB C device that support DisplayPort Alternate Mode(display output)

## 【Attention】

1.System environment compatible with: Windows/Linux/Mac OS/Android.

# Technical data sheet

CU520M

USB C/M to C/M Cable with IC 20Gbps USB4 Aluminum shell

---

- 2.If the device is forcibly removed, it may cause data or disk errors, damage and loss, please follow the specifications for device removal operation.
3. Do not place the product in an environment where corrosive substances are present.
4. Do not place the product and accessories in apparatus with strong electromagnetic fields and keep away from magnetic devices.
5. Do not hit, throw or pinch the product, avoid dropping, crushing or bending the product.
6. Do not place the product in high temperature, low temperature, humid, dusty or exposed to sunlight for a long period of time, and keep away from fire sources.