







REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	Engineering Release	3/16/2018	M.C.



FLAT FACE LENS

DIMENSIONS ARE APPLICABLE TO BOTH LENS FACES UNLESS OTHERWISE NOTED



PART NUMBER CONFIGURATION
(SEE PAGE 2, TABLES A & B)
LPV4-XXXXXP

LENS FACE

HEIGHT, (H)

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 BIVAR [®] 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR		
.X ± .1	X° ± 1°		
.XX ± .01		TITLE: BIVAR LIGHT PIPE SYSTEM, VERTICAL, 4MM, SINGLE STATION	REVISION: A
.XXX ± .005			
DESIGNED: K. BARON	DATE: 03/16/18	PART NO.: LPV4-XXXXXP	
REVISED: N/A	DATE: N/A	CAGE CODE: 32559	
CHECKED: TD. NGUYEN	DATE: 03/16/18	SCALE: 2:1	SHEET # 1 OF 2

CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
	See Sheet 1		

STANDARD ORDERING INFORMATION

TABLE A - FLAT FACE LENS	
PART NO.	H ±.01
LPV4-0350FP	0.350 [8.9mm]
LPV4-0400FP	0.400 [10.2mm]
LPV4-0450FP	0.450 [11.4mm]
LPV4-0500FP	0.500 [12.7mm]
LPV4-0550FP	0.550 [14.0mm]
LPV4-0600FP	0.600 [15.2mm]
LPV4-0750FP	0.750 [19.1mm]
LPV4-1000FP	1.000 [25.4mm]
LPV4-1250FP	1.250 [31.8mm]
LPV4-1500FP	1.500 [38.1mm]
LPV4-1750FP	1.750 [44.5mm]
LPV4-2000FP	2.000 [50.8mm]

TABLE B - DOME FACE LENS	
PART NO.	H ±.01
LPV4-0350DP	0.350 [8.9mm]
LPV4-0400DP	0.400 [10.2mm]
LPV4-0450DP	0.450 [11.4mm]
LPV4-0500DP	0.500 [12.7mm]
LPV4-0550DP	0.550 [14.0mm]
LPV4-0600DP	0.600 [15.2mm]
LPV4-0750DP	0.750 [19.1mm]
LPV4-1000DP	1.000 [25.4mm]
LPV4-1250DP	1.250 [31.8mm]
LPV4-1500DP	1.500 [38.1mm]
LPV4-1750DP	1.750 [44.5mm]
LPV4-2000DP	2.000 [50.8mm]

BIVAR [®]		REVISION:
PART NO: LPV4-XXXXXP		A
SCALE: N/A	SHEET # 2 OF 2	
CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

[LPV4-1000FP](#) [LPV4-1500DP](#) [LPV4-0500DP](#) [LPV4-0550FP](#) [LPV4-1750FP](#) [LPV4-0350FP](#) [LPV4-1250DP](#) [LPV4-0450DP](#) [LPV4-0400DP](#) [LPV4-0400FP](#) [LPV4-0550DP](#) [LPV4-2000DP](#) [LPV4-0600FP](#) [LPV4-0750DP](#) [LPV4-0600DP](#) [LPV4-0350DP](#) [LPV4-2000FP](#) [LPV4-1000DP](#) [LPV4-1250FP](#) [LPV4-1500FP](#) [LPV4-0450FP](#) [LPV4-1750DP](#) [LPV4-0500FP](#) [LPV4-0750FP](#)