


2.5mm 90° Mono Phone Plug

172-2009, 172-2019, 172-2069

KOBICONN

2.5mm 90° Mono Phone Plug



DIMENSIONS: IN

SPECIFICATIONS

Type:	2.5mm Mono Plug, Right Angle, Stripped & Tinned
Cable:	(10/0.12 + 30/0.12) x IC
O.D.:	0.138
Jacket:	IC Shield with Black PVC
Temperature:	60°C
Voltage:	24VDC

Mouser Stock No.	Length
172-2009	36±1.181
172-2019	120±3.937
172-2069	72±1.969

Date Last Revised: 4-6-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300319

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[172-2009](#) [172-2069](#) [172-2019](#)