									1	
							REV.	DATE	DESCRIPTION	
							A	02/09/06	UPDATE DRAWING FORMAT	
							В	05/08/07	REVISE BARREL, FERRULE DIMENSIONS	
	2.0	00 [.079]	RECOMMENT		5.20 [.205]					
$6.00 [.236] \underbrace{-16.00 [.236]}_{16.00 [.630]} \underbrace{-16.00 [.236]}_{16.00 [.236]} \underbrace{-16.00 [.236]}$										
	NOTE: 19.3 [.761] NOTE: 1. CRIMPED FERRULE HEX CRIMP SIZE .128" 2. CRIMPED CONTACT PIN SQ. CRIMP SIZE 0.7mm									
_			1							
					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERANCE ONLY.	APPROVALS	DATE		Amphanal Canner	
,					UNLESS OTHERWISE SPECIFIED	DRAWN G.R.S.	05/08/0	7	Amphenol Connex	
5					TOLERANCES FOR MILLIMETERS ARE: $0.5 - 8mm \pm 0.20mm$	CHECKED	,, •			
5	HEAT SHRINK TUBE			1	8 – 30mm ± 0.40mm			PART DESCR	SMB CRIMP JACK	
4	FERRULE	COPPER	GOLD	1	30 – 120mm ± 0.50mm	ISSUED				
3	CONTACT PIN	BRASS	GOLD	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:	SHEET 1 OF 1		_	(FOR 174/U, 188A/U, 316/U CABLE)	
2	INSULATOR	TEFLON	NATURAL	1	$.020315 = \pm 0.007"$	SHEET 1 OF 1		PART NO.		
1	BODY	BRASS	GOLD	1	$.315 - 1.180 = \pm 0.015"$ $1.180 - 4.724 = \pm 0.020"$				142189	
	DESCRIPTION	MATERIAL	FINISH	QTY		CAD FILE	00.000	DWG. NO.	142189.DWG REV. B SIZE A SCALE NA	
	DESCRIPTION			WII	DO NOT SCALE DRAWING	C:/142/142189.DWG			142189.DWG REV. B SIZE A NA	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol: 142189