





PLIO

Material: tinned copper
 Insulation: polypropylene
 Temperature of use: +105°C maxi (120°C short time)



• PLIO bootlace insulated ferrules



type	article number	section mm ²	insulator colours	a	L	dimensions (mm)			*
						d1	d2	d4	
PLIO - 0,5	0649 0005 000	0,5	white	8	13,5	1,1	1,4	2,5	1000
PLIO - 0,75	0649 0010 000	0,75	blue	8	14	1,3	1,6	2,8	1000
PLIO - 1	0649 0015 000	1	red	8	14	1,5	1,8	3	1000
PLIO - 1,5	0649 0020 000	1,5	black	8	14	1,8	2,1	3,4	1000
PLIO - 2,5	0649 0030 000	2,5	grey	8	15	2,3	2,6	4,2	1000
PLIO - 4	0649 0040 000	4	orange	9,5	16,8	2,9	3,2	4,8	1000
PLIO - 6	0649 0050 000	6	green	12	20	3,5	3,9	6,2	500
PLIO - 10	0649 0060 000	10	brown	12	21	4,6	5	7,5	500
PLIO - 16	0649 0070 000	16	white	12	23	5,8	6,2	8,8	500
PLIO - 25	0649 0080 000	25	black	16	29	7,3	7,7	11	50
PLIO - 35	0649 0090 000	35	red	16	30	8,3	8,7	12,5	50
PLIO - 50	0649 0100 000	50	blue	20	36	10,3	11	15	50



* string bags

• PLIO bootlace ferrules for two conductors especially for bridges or looping-in of two conductors on the same contactor

type	article number	section mm ²	insulator colours	a	L	dimensions (mm)				*
						d1	d2	d4	d5	
PLIO - 2 x 0,5	0649 0210 000	2 x 0,5	white	8	15	1,5	1,8	4,5	2,3	1000
PLIO - 2 x 0,75	0649 0220 000	2 x 0,75	grey	8	15	1,8	2,1	5,1	2,6	1000
PLIO - 2 x 1	0649 0230 000	2 x 1	red	8	15	2,05	2,35	5,1	3	1000
PLIO - 2 x 1,5	0649 0240 000	2 x 1,5	black	8	16	2,3	2,6	6,4	3,5	1000
PLIO - 2 x 2,5	0649 0250 000	2 x 2,5	blue	10	18,5	2,3	2,9	7,5	4	1000
PLIO - 2 x 4	0649 0260 000	2 x 4	grey	12	23	3,8	4,2	8,6	4,9	1000
PLIO - 2 x 6	0649 0270 000	2 x 6	yellow	14	25	4,9	5,3	9,6	5,8	500
PLIO - 2 x 10	0649 0280 000	2 x 10	red	14	26	6,5	6,9	12,6	7	500



B7/5






BOX 1 - BOX 2

Specifications: **stacking** (with central hole of 7 mm)
rotating lid with window.

Applications: round dispenser box. **Ideal for work on site.**

A wide range of permanently available connectors
No loss of time.




type	article number	Ø mm	height mm	weight g	
Box 1 - 180012	0649 0810 000	90	40	90	1
contents	section (mm ²)	quantity			
	0,5	50			
	0,75	100			
	1	100			
	1,5	100			
	2,5	50			
Box 2 - 180022	0649 0820 000	90	40	85	1
contents	section (mm ²)	quantité			
	4	50			
	6	20			
	10	20			
	16	10			

BOX 3

Applications: rectangular dispenser box. **Ideal for work on site.**

A wide range of permanently available bootlace ferrules and crimping tool.
No loss of time.




type	article number	dimensions mm	weight g	
Box 3 - SO5252Z	0649 0830 000	210x120x35	410	1
contents	section (mm ²)	quantity		
	0,5	100		
	0,75	100		
	1	150		
	1,5	150		
	2,5	100		
	4	50		
	K4 crimping tool for bootlace ferrules of 0,5 to 2,5 mm ²			





Bootlace ferrules

Material: tinned electrolytic copper
Material insulation: polypropylene
Operating temperature: +105°C maxi (120°C short time)



type for section (mm ²)	article number	colour	in reels of	dimensions (mm)						
				a	L	d1	d2	d4		
Bandoliered bootlace ferrules in bags										
WH 0,5 mm ²	0649 0105 001	white	10 x 50 ferrules	8	13,5	1,1	1,4	2,5	500	
BU 0,75 mm ²	0649 0110 002	blue	10 x 50 ferrules	8	14	1,3	1,6	2,8	500	
RD 1 mm ²	0649 0115 007	red	10 x 50 ferrules	8	14	1,5	1,8	3	500	
BK 1,5 mm ²	0649 0120 010	black	10 x 50 ferrules	8	14	1,8	2,1	3,4	500	
GY 2,5 mm ²	0649 0130 013	grey	10 x 40 ferrules	8	15	2,3	2,6	4,2	400	
Bandoliered bootlace ferrules in dispenser boxes										
YE 0,25K mm ²	0649 0301 004	white	1000 ferrules	8	12,5	0,8	1,3	2	1000	
TQ 0,35K mm ²	0649 0303 086	turquoise	1000 ferrules	8	12,5	0,8	1,3	2	1000	
WH 0,5K mm ²	0649 0305 001	yellow	1000 ferrules	8	13,5	1,1	1,4	2,5	1000	
BU 0,75K mm ²	0649 0310 002	blue	1000 ferrules	8	14	1,3	1,6	2,8	1000	
RD 1K mm ²	0649 0315 007	red	1000 ferrules	8	14	1,5	1,8	3	1000	
BK 1,5K mm ²	0649 0320 010	black	1000 ferrules	8	14	1,8	2,1	3,4	1000	
GY 2,5K mm ²	0649 0330 013	grey	500 ferrules	8	15	2,3	2,6	4,3	500	
Bandoliered bootlace ferrules on reels										
WH 0,5D mm ²	0649 0306 001	white	3000 ferrules	8	13,5	1,1	1,4	2,5	3000	
BU 0,75D mm ²	0649 0311 002	blue	3000 ferrules	8	14	1,3	1,6	2,8	3000	
RD 1D mm ²	0649 0316 007	red	3000 ferrules	8	14	1,5	1,8	3	3000	
BK 1,5D mm ²	0649 0321 010	black	2500 ferrules	8	14	1,8	2,1	3,4	2500	
GY 2,5D mm ²	0649 0331 013	grey	1500 ferrules	8	15	2,3	2,6	4,3	1500	



bandoliered bootlace ferrules in dispenser boxes



bandoliered bootlace ferrules on reels



crimping machine MC 25 for bandoliered bootlace ferrules
Please contact our technical department.

