

## Data Sheet | Item Number: 261-317/331-000

2-conductor terminal block; on one side with push-button; with snap-in mounting foot; 1-pole; for plate thickness 0.6 - 1.2 mm; Fixing hole 3.5 mm Ø; 2.5 mm<sup>2</sup>; CAGE CLAMP®; 2,50 mm<sup>2</sup>; green-yellow

<https://www.wago.com/261-317/331-000>



Color:  green-yellow

Similar to illustration



Similar to illustration

### Connection data

Connection points	2
Total number of potentials	1
Number of levels	1

### Connection 1

Connection technology	CAGE CLAMP®
Actuation type	Operating tool
Connectable conductor materials	Copper
Solid conductor	0.08 ... 2.5 mm <sup>2</sup> / 28 ... 14 AWG
Fine-stranded conductor	0.08 ... 2.5 mm <sup>2</sup> / 28 ... 14 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches
Pole number	1
Wiring direction	Side-entry wiring

### Connection 2

Actuation type 2	Push-button
------------------	-------------

### Physical data

Width	6 mm / 0.236 inches
Height from the surface	23.3 mm / 0.917 inches
Depth	28.1 mm / 1.106 inches

### Mechanical Data

Design	horizontal type
Mounting type	Snap-in foot
Marking level	Side marking

## Material Data

Note (material data)

[Information on material specifications can be found here](#)

Color green-yellow

Material group I

Insulation material Polyamide (PA66)

Flammability class per UL94 V0

Fire load 0.054 MJ

Halogen-free Yes

Weight 2.5 g

## Commercial data

eCl@ss 10.0 27-14-11-06

eCl@ss 9.0 27-14-11-06

ETIM 8.0 EC001284

ETIM 7.0 EC001284

PU (SPU) 200 (50) pcs

Packaging type Box

Country of origin DE

GTIN 4044918626088

Customs tariff number 85369010000

## 1 Compatible Products

### 1.1 Required Accessories

#### 1.1.1 End plate

##### 1.1.1.1 End plate

**Item No.: 261-371**

End plate; with snap-in mounting foot; gray